

# DV-7000 Heli-Flow® Pump

Servo-controlled auger pump

## Features and Benefits

- **Footed cartridge with a fixed mechanical stand-off nozzle for extremely consistent dots and increased throughput**
- **Luer-cartridge option allows use with a wide range of standard needles**
- **Tool-free disassembly of wetted parts for quick and easy cleaning**
- **Fast cartridge changeover**
- **Cartridges are interchangeable with DV-8000 pumps**



The DV-7000 Heli-Flow® pump is available in a luer- or footed-needle design with interchangeable cartridges, allowing each pump to work with several different fluid types. The DV-7000 has a hardened auger for use with filled epoxy materials and features a high flow rate.

Footed needle cartridges feature an accurate and consistent gap between the needle tip and the foot. The foot contacts the board, and the gap ensures that the pump dispenses fluid at a programmable distance from the board surface and compensates for variations in the board's surface, providing fast small-dot dispensing. Typical applications include solder paste, silver paste, and dispensing small-dot surface mount adhesives.

Luer-lock needle cartridges use the needle with a height sensor to set the gap between the board surface and needle tip, and is ideal for applications when the needle can't touch the board. Applications include dam writing, area fills, glob top, and lid seal.

The quick-release cartridge design of the DV-7000 makes cleaning easy. Simply press the quick release lever to remove the needle and cartridge. No tools are required. To use a different fluid type, simply change the cartridge, needle, and disposable fluid line.

Nordson ASYMTEK's other auger pump – the DV-8000 with its fixed-head design – is ideal for high flow rate encapsulation and lid seal applications. The DV-7000 pump is interchangeable with DV-8000 cartridges, although only the DV-7000 can use footed cartridges. Both pumps cover a wide range of dispensing applications to provide flexible process solutions.

**motralec**

4 rue Lavoisier . ZA Lavoisier . 95223 HERBLAY CEDEX  
Tel. : 01.39.97.65.10 / Fax. : 01.39.97.68.48  
Demande de prix / e-mail : [service-commercial@motralec.com](mailto:service-commercial@motralec.com)

[www.motralec.com](http://www.motralec.com)

**Nordson**  
ASYMTEK


## Specifications: DV-7000 Pump

Parameter	Specification
Dimensions	Length: 190-192 mm (7.48-7.56 in.) Width: 33 mm (1.3 in.) Depth: 72.6 mm (2.86 in.)
Air pressure required	34-552 kPa (5-80 psi, 0.7 -5.5 bar) Higher fluid viscosities require higher pressures
Motor	Closed-loop control with encoder feedback on the dispensing platform

### Pump configurations

Model	Description	Application
DV-7222-SF1	Footed needle cartridge	Surface mount adhesive, solder paste, silver epoxy
DV-7222-SL1	Luer-lock needle cartridge	Surface mount adhesive, solder paste, silver epoxy
DV-7223-CP8-LP	Precision needle cartridge	Silver epoxy, Types 3 and 4 solder pastes
DV-7223-CP0-LP	Precision needle cartridge	Types 5 and 6 solder pastes
DV-7321-CL8	Luer-lock needle cartridge	Dam writing
DV-7322-CL8	Luer-lock needle cartridge	Glob top, encapsulation
DV-7331-CL8	Luer-lock needle cartridge	Lid seal

### Fast and easy cartridge loading



motralec

4 rue Lavoisier . ZA Lavoisier . 95223 HERBLAY CEDEX  
Tel. : 01.39.97.65.10 / Fax. : 01.39.97.68.48  
Demande de prix / e-mail : [service-commercial@motralec.com](mailto:service-commercial@motralec.com)

[www.motralec.com](http://www.motralec.com)